smiths interconnect

HyperGrip[®] Series

High Reliability Medical Circular Connectors



Available Contact Technologies

Features and Benefits

Hypertac[®] Hyperboloid - HC

Long contact life

Industry-leading mating cycles (over 20,000) provide low cost of ownership

Low insertion/extraction forces

Ergonomic mating without cost and size of mate assist hardware

- Lower contact resistance Low power consumption / lower voltage drop across connector
- Higher current ratings Smaller contacts needed to carry power for reduced size and weight
- Immunity to shock and vibration Reliability under harsh environmental conditions
- Self-cleaning contacts assure uninterrupted connection
- RoHS compliance



Screw-machined contact - MR

Medium contact life

Mechanical life minimum 2,000 cycles

Flexible design

The inner clip and the socket body are manufactured and plated separately

Reliable and cost effective

The production of machined specific contact bodies allows for high volumes and low costs

Low insertion/extraction forces

Ergonomic mating without cost and size of mate assist hardware

Low contact resistance

Low power consumption / lower voltage drop across connector

Higher current ratings

Small contacts needed to carry power for reduced size and weight

RoHS compliance





smiths interconnect

Contents

HyperGrip [®] Series	2
Features and Benefits	2
How To Order	3
Technical Characteristics	4
Dimensions	
Plug and Receptacle	5
Disposable HG2 and HG4 Plugs	6
Keying and Mounting	
Receptacle Keying	7
Panel Cutouts	7
Receptacle Mounting Options	8
Additional Contact Technologies	9
Applications	9



HyperGrip[®] Series



HyperGrip Circular Connector Series is available with 5, 12, 19, or 33 pin positions and a user-configurable keying system. While competitive products require purchasing a different connector for each keying configuration needed, our advanced keying system allows customers to build connectors with six different keying options reducing lead time and inventory.

Specifically designed to meet medical industry requirements, the HyperGrip connector's sleek, robust body delivers superior performance in the most crucial applications. Not only does the standard sealing offer IP65 protection when mated to prevent electrical shorts, but the available shielding feature supplies EMI/ RFI protection providing the highest degree of safety and reliability.

By utilizing the unparalleled performance of Hypertac[®] hyperboloid contact technology and the flexible and reliable design of the MR contact, HyperGrip connectors are able to provide high cycle life, low power consumption, low insertion force, reliability under harsh conditions, maximum contact performance and excellent wiping action.

HyperGrip connectors are color-coded and range from ~12.5 to 22.5 mm in diameter. The five available color options, along with our innovative keying system, make recognition effortless and incorrect mating impossible. This becomes essential for medical instrumentation applications where multiple connector interfaces are required. The Series includes disposable plugs for HG2 and HG4 sizes designed to support overmolding and high volume production methods and to withstand at least 30 cycles whilst ensuring the connector performance in terms of insulation resistance, dielectric withstanding voltage, current carrying, and low level current resistance.

Smiths Interconnect offers custom options in order to meet application specific requirements. The flexible design of HyperGrip connectors allows for the use of alternate technologies including fiber optic (expanded beam or butt joint termini), coaxial and spring probe contacts. Custom inserts, cable mount receptacles and cable assemblies (available in select sizes) can also be provided to optimize your connector solution.

Designed to meet medical industry requirements

Features and Benefits

- Push/pull latching feature, quick connect Simple one-hand mating/unmating
- Innovative customer keyability Easily keyed in 6 standard positions to prevent mismating
- Available with 5 color code options Visually intuitive mating
- Sleek, robust body Designed to aesthetically complement medical devices
- Sealing to IP65 when mated Meets or exceeds typical medical sealing requirements
- Fingerproof

Meets requirements of IEC 60601-1 specifications

- Multiple contact technologies available Flexibility for superior performance in high reliability, high speed, high density, high frequency and/or hybrid solutions
- Shielding option available in HG2, HG3 and HG4 Protection against EMI/RFI interference
- Disposable option for HG2 and HG4 plugs

Single use disposable plugs designed to support overmolding / high volume production methods and to withstand at least 30 cycles

- Autoclave, EtO and Sterrad[®] sterilizable Meets typical medical sterilization requirements
- UL94 flammability rated materials Meets medical industry safety requirements
- Integrated strain relief Prevents cable wire fatigue due to bending
- Contacts shipped unloaded

Easier termination for reduced cost of ownership: crimp and poke termination eliminates the need to pre-tin, solder, and shrink boot

2

smiths interco	nnect		HyperGrip [®] Series							
How To C)rder									
H G 1 2 3	G 4 5 6 7	8	9 10	R 11 1	12 13					
1 Series	H G _{Series}									
2 Size	0 _{HG0} . 2 _{HG2}	3 _{HG3}	4 HG4							
3 Туре	P Plug E Receptacle/I	C Receptac (Available or								
	D Disposable plug									
4 Connector option	1 Sealed 2 Shielded (Unsealed) HG2, HG3, HG4 only / plugs "P" and panel receptacles "E" only)									
5 Strain relief size (Cable diameter ranges)	0 No strain relief	4.50 mm (HG2 only)	o 6.50 mm (HG4 only) (Shielded: 9.50 mm to 11.00 mm)							
	1 2.08 mm to 3.10 mm (HG0 only)	5 7.00 mm t (HG3 only)	to 9.00 mm							
6 Outer shell color	G Light gray W White (Disposable only)									
7 Color coding (Strain relief or panel seal only)	G Light gray (Standard)	D Blue	R Red	V Green	Y Yellow					
8 Positions	G _{HG0} 1 2 _{HG2}	1 9 _{HG3}	3 3 _{HG4}							
9 Contact diameter	0 3 0.3 mm (HG0)	0 4 0.4 mm	n (HG2, HG3, HG	4)						
10Contact gender	Female sockets (Receptacles only)	Male pins (Plugs only)								
11 Termination (Fixed)	R Crimp/Solder (26–28 AWG ^{**}) (Contacts are shipped unloaded, may be crimped or soldered, then inserted into insulator. For more information, please see Assembly Instructions.)									
12 Plating (Pins: Gold over nickel	G HG2, HG3, HG4 pins		H HGO pins							
Sockets: Gold over nickel on contact surfaces, gold flash on terminations)	A N H HG2, HG3, HG4 HC soc	kets	A H HGO HC sockets							
	HG2, HG3, HG4 MR sockets		A 2 Dispos	able HG2, HG4 pi	ins					
13Keying option (Disposable only)	- A _{A-Key}	- B _{B-Key}								
	- C _{C-Key}	- D _{D-Key}								
	- E _{E-Key}	- F _{F-Key}								

Not available for HG versions with MR contact
Available tooling: Crimp Tool: AFM8 or M22520/2-01, Crimp Positioner: K1775 (HGO) or T2030 (HG2, HG3, HG4), Insertion Tool: T2080
Disposable plug is available only for 12 and 33 positions
Disposable plug only uses 0.4 mm contacts

Technical Characteristics

	HGO	HG2	HG3	HG4						
Number of contacts	5	12	19	33						
Contact diameter in inches (mm)	0.012 (0.30)	0.016 (0.40)	0.016 (0.40)	0.016 (0.40)						
Materials	,	·								
Body	Polyetherimide									
Insulators	Liquid crystal polymer									
Seals	Silicone									
Contact Materials and Plating)									
	Н	С	М	R						
Sockets	Beryllium copper wires Brass body components Gold over nickel plating o Gold flash over nickel on		Beryllium copper clip Copper-zinc-lead body component Gold plating over Nickel underplating							
Pins	Phosphor bronze Gold over nickel plated									
Terminations										
	26 to 28 AWG									
Crimp (Pin and Socket)	Optional terminations, including solder cup and straight-dip pc tails (for panel mount receptacles), are spec order only. Please contact factory for availability.									
Shielding (Optional)										
Effectiveness	Up to 3 GHz									
Attenuation	50 dB maximum at 3 GHz									
Mechanical										
Mating cycle life	Up to 20,000 with Hyper	boloid contact - Up to 2,0	000 with MR contact							
Contact extraction force	0.50 to 1.60 oz. per contact									
Electrical										
Current rating (A) (per contact, with all contacts energized)	5.5	3	2.5	1						
Contact resistance	Hyperboloid Contacts < 8.0 m Ω - MR Contacts and Disposable Options < 12.0 m Ω									
Breakdown voltage between contacts	1,000 V max.									
Dielectric withstanding voltage	1125 V									
nsulation resistance	> 5×104 MΩ at 500 VDC									
Physical and Environmental										
Operating temperature rating	-40°C to 125°C									
Processing temperature range	Up to 185 °C									
Flammability	Materials meet the requirements of UL94									
Sterilization	Steam autoclave, EtO, Sterrad ^{®2}									

Notes:

Fingerproofing

Sealing (mated condition)

IP65

 HyperGrip is patented under US patent numbers: 7,326,091B2; 7,661,995B2; D596,127S; 7,938,670; D615,932; D616,825
Sterrad® is a registered trademark of Advanced Sterilization Products (ASP) division of Ethicon US, LLC, a Johnson & Johnson Company. Dimensions are in inches (mm)

Meets IEC 60601-1 requirements


Dimensions

Standard HyperGrip[®] connectors


Plug and Receptacle HGO, HG2, HG3 and HG4


Plug and receptacle mated pair

With strain relief




With shielding option







P HG2 plug




HG2 Plug and Cable Receptacle


HG2 Plug and cable receptacle mated pair

With strain relief



C HG2 cable receptacle






	Dimensions													
	Α	В	С	D	E	F	G	н	J	K	L	Μ	Ν	Ρ
HGO	Ø0.807 (20.50)	0.728 (18.50)	Ø0.630 (16.00)	0.285 (7.25)	1.040 (26.38)	0.343 (8.71)	Ø0.370 (9.40)	Ø0.486 (12.34)	1.415 (35.94)	0.118 (3.00)	0.689 (17.50)			—
HG2	Ø1.014	1.220	Ø0.866	0.272	1.808	0.427	Ø0.502	Ø0.656	2.390	0.118	0.823	Ø0.449	Ø0.346	1.704
	(25.76)	(30.88)	(22.00)	(6.91)	(45.92)	(10.84)	(12.75)	(16.66)	(60.65)	(3.00)	(20.90)	(11.40)	(8.80)	(43.27)
HG3	Ø1.172	1.220	Ø1.007	0.272	2.170	0.354	Ø0.650	Ø0.800	2.730	0.118	0.980	Ø0.535	Ø0.378	1.961
	(29.77)	(30.88)	(25.59)	(6.91)	(55.07)	(9.00)	(16.50)	(20.36)	(69.33)	(3.00)	(24.90)	(13.60)	(9.60)	(49.82)
HG4	Ø1.250	1.220	Ø1.090	0.272	2.170	0.354	Ø0.710	Ø0.880	2.730	0.118	1.060	Ø0.610	Ø0.378	2.124
	(31.77)	(30.88)	(27.80)	(6.91)	(55.07)	(9.00)	(18.15)	(22.47)	(69.33)	(3.00)	(76.90)	(15.50)	(9.60)	(53.95)


Dimensions are in inches (mm)

Disposable HG2 and HG4 Plugs

Plug and receptacle mated pairs HG2


HG4





Disposable HG2 plug


With strain relief





Disposable HG4 plug

With strain relief





6

В

0.240 (6.10)

0.329 (8.36)

0.393 (9.98)

0.430 (10.92)

Keying and Mounting


(User information)

Receptacle Keying

HG2 shown (HG0, HG3 and HG4 are keyed in the same fashion). 6 different keying positions are possible - A through F

Keying position A

Receptacle wiring end



See Assembly Instructions for receptacle keying information¹:

S50386: Panel Receptacles

S50431: Cable Receptacles

Panel Cutouts

A +0.002 -0.001 (+0.050 -0.030) HGO Ø0.555 (14.10) HG2 Ø0.711 (18.06) HG3 Ø0.870 (22.10) HG4 Ø0.949 (24.10)


Dimensions are inches (mm)

Notes:


1) Instructions also include plug keying information: S50387

Receptacle Mounting Options

Assemble outside panel then install



Install receptacle body then assemble inside panel



Notes:

Recommended tightening torque for panel mount receptacle for HG2, HG3, and HG4 is 0.452 Nm to 0.678 Nm. The recommended tightening torque for HG0 is 0.226 Nm to 0.339 Nm.

Additional Contact Technologies*

(Features and Benefits)

Spring Probe

- Extremely high density
- Shock and vibration resistant
- Exceptional misalignment tolerance
- High cycle life
- Z-axis compliance







Fiber Optic

- Two standard types:
 - Size 16 butt-joint
 - Size 12 expanded-beam (EB) termini
- Low insertion loss
- Hermaphroditic contacts (butt joint)
- Multi and single-mode fiber compatible (EB)
- Low susceptibility to contamination (EB)
- Resistant to EMI/RFI and crosstalk

Coaxial

- 50Ω characteristic impedance
- Crimp termination for RG-405 Flex Cable
- Low VSWR up to 40 GHz
- Magnetic permeability: 30×10-5µr
- Immunity to shock and vibration
- Up to 20K mating cycles

Applications

Catheter

- Disposable
- High density spring probe contacts
- High cycle life
- Low contact resistance
- Minimal insertion/ extraction forces

Patient monitoring

- Hvperboloid signal contacts
- Custom creepage and clearance
- High reliability
- -Cost effective
- Patient friendly

Portable therapeutic

- Custom cable solution
- Superior reliability for critical application
- Color coded
- Multiple keys to prevent mismating
- Intuitive design

MRI/CT scanning

- latching Hyperboloid
- options

Surgical imaging

- Expanded beam fiber optic contact
- Low susceptibility to contamination
- Fiber optic video connection for easy mating to HD display system

Home healthcare

- Hyperboloid and USB signal contacts
- IP65 sealing
- Simple operation
- Ergonomic, ideal for in-home patient use

- ESD finger-proof protection

Ouick push/pull

- signal contacts

- Multiple keying

Worldwide Support

Connectors

Americas

Sales connectors.uscsr@smithsinterconnect.com

Technical Support connectors.ustechsupport@smithsinterconnect.com

Ευгоре

Sales connectors.emeacsr@smithsinterconnect.com

Technical Support connectors.emeatechsupport@smithsinterconnect.com

Asia

Sales asiacsr@smithsinterconnect.com

Technical Support asiatechsupport@smithsinterconnect.com

Fiber Optics & RF Components

Americas

Sales focom.uscsr@smithsinterconnect.com

Technical Support focom.techsupport@smithsinterconnect.com

Ευгоре

Sales focom.emeacsr@smithsinterconnect.com

Technical Support focom.techsupport@smithsinterconnect.com

Asia

Sales focom.asiacsr@smithsinterconnect.com

Technical Support focom.techsupport@smithsinterconnect.com

Semiconductor Test

Americas

Sales semi.uscsr@smithsinterconnect.com

Technical Support semi.techsupport@smithsinterconnect.com

Еигоре

Sales semi.emeacsr@smithsinterconnect.com

Technical Support semi.techsupport@smithsinterconnect.com

Asia

Sales semi.asiacsr@smithsinterconnect.com

Technical Support semi.techsupport@smithsinterconnect.com

RF/MW Subsystems

Americas, Europe & Asia

Sales subsystems.csr@smithsinterconnect.com

Technical Support subsystems.techsupport@smithsinterconnect.com

Connecting Global Markets

more > smithsinterconnect.com

Copyright© 2023 Smiths Interconnect | All rights reserved | Version 3.1 All of the information included in this catalogue is believed to be accurate at the time of printing. The information contained within this document is subject at all times to applicable Export Control regulations and legal requirements.